



When deployed as part of an Inovonics mobile duress or senior living system, EN5060 locators help determine precise floor and room location for alarm events to improve response times.

Product Features

Provides precise location for alarm events when used with Inovonics location-enabled pendants

LED flashes with all transmissions, ensuring operation at a glance

Outlet mount provides flexibility for installation

24/7 monitoring to maintain system health

Works with existing Inovonics security and senior living systems, eliminating forklift upgrades

Product Specifications

Dimensions:	2.47" x 5.58" x 2.20" (63 mm x 142 mm x 56 mm.)
Weight:	6.3 oz (179 g)
Power requirement:	Standard 115-120VAC 50-60Hz wall sock
Operating environment:	
Temperature:	-4 to 167°F (-20 to 75°C)
Environment:	90% relative humidity, non-condensing
Market:	North America
EchoStream® frequency:	902-928 MHz, frequency hopping spread spectrum
Bluetooth® frequency:	2.402 GHz to 2.480 GHz
Compatible gateways:	EN7295 mobile duress gateway; EN7380 senior living gateway
Check in time:	60 minutes
Regulatory compliance:	FCC Part 15, Subpart C, RSS-247 Issue 2, RoHS Directive 2015/86
UL certification:	UL and cUL Listed to UL 62368-1, audio/video, information and communication technology equipment

Reference Materials (available at www.inovonics.com)

[EN5060 Locator Installation Instructions](#)

[Mobile Duress Application User Manual](#)

[Location Solution Brochure](#)

- The range and performance of any wireless product depends on the structure and environment in which it operates.
- Continual enhancements to our products may cause specifications to change without notice.
- Patents: 7,154,866; 7,554,932; 7,746,804; others pending.
- Inovonics supports recycling and reuse whenever possible. Please recycle these parts using a certified electronics recycler.

Technical documents

For technical documents visit us at <http://www.inovonics.com/support/tech-documents/> or use the QR code below.

